



AVT-501/502/503

Vortex Mixer Adjustable Speed



AVT-501



AVT-502

Key Features

- ⦿ Fixed Speed Touch Mode-Sample,economic and high power stirring;
- ⦿ Dual Speeds and Dual Modes-Selective modes(Touch and Continuous)with selective (2800rpmfor Touch and 1200rpm for Continuous);
- ⦿ Two Modes and Adjustable Speed.

Product Description

Vortex Mixer:

1. Fixed Speed Touch Mode-Sample,economic and high power stirring;
2. Dual Speeds and Dual Modes-Selective modes(Touch and Continuous)with selective speed (2800rpm for Touch,and 1200rpm for Continuous);
3. Two Modes and Adjustable Speed.



⦿ Specifications:

Model	AVT-501	AVT-502	AVT-503
Speed (rpm)	1000 in continuous mode and 2800 in touch mode	2800	Digital display, adjust speed 2800rpm
Orbit. (mm)	4.2		
Action Type	Touch and continuous	Touch	Touch and continuous
Type of Accessories	1 rubber cup and plastic adapter	1 rubber cup	1 rubber cup
Maximum Load (kg)	1	1	1
Net Weight (kg)	3.2	3.2	3.2
Power Supply	AC-DC Adapter, UL and rated AC input: 90-230V, DC output: 6V,3A		220V+/-10% or 110v+/-10%

Accessory Code	Description
AVT-01	Rubber Cup
AVT-02	Plate Adapter with Rubber Disc
AVT-03	Plain Adapter Foam
AVT-04	Foam with 96X0.2 well
AVT-05	Foam with 60X0.5 well
AVT-06	Foam with 12mm well
AVT-07	Foam with different well.